SILICONE EDGE FABRIC - CÓMO MEDIR EL MARCO

1 MEASURE THE FRAME



Measure the outermost dimensions of the Silicone Edge Graphic (SEG) frame.

Use the inches side of the tape measure to record the width from side to side, and the height from top to bottom.

* If the frame was provided by 40 VISUALS skip to step 3. There is no need for any more measurements other than the frame dimensions.

2 MEASURE THE FRAME CHANNEL



Measure the frame channel , the groove around the perimeter of the frame, where the silicone beading is inserted. This thickness varies depending on the frame manufacturer.

Pull a section of the graphic from the frame to access the frame channel.

Use the millimeter side of the tape measure held straight across the channel at any point.

Snap a photo of the channel next to the tape measure .

3 SEND THE DIMENSIONS



Email the outer frame dimensions (in inches) and a photo of the frame channel thickness (in millimeters) to measurements@40visuals.com

Be sure to include your store or company name in the subject line!

